



Be Right™



Encapsulated Differential pH Sensor, LCP (Liquid Crystal Polymer) Body, 5-Wire with Internal Preamplifier, Glass Electrode, 90 ft Cable

Product #:

6028P090

INR Price:

Contact Hach

Ships within 2 weeks

 **Hazardous**

Items with this mark may be considered hazardous under some shipping conditions.

If necessary, we will change your selected shipping method to accommodate these items.

LCP (Liquid Crystal Polymer), Convertible Mounting Style, 27.5m Analog Cable, 5-Wire with Built-In Preamplifier, General Purpose Glass pH Electrode, 90 ft Cable

Exceptional Performance with the Differential Electrode Measurement Technique

This field-proven technique uses three electrodes instead of the two normally used in conventional pH sensors. Process and reference electrodes measure the pH differentially with respect to a third ground electrode. The end result is unsurpassed measurement accuracy, reduced reference junction potential, and elimination of sensor ground loops. These sensors provide greater reliability, resulting in less downtime and maintenance.

Lower Maintenance Needs with the Replaceable Salt Bridge

The salt bridge creates a barrier to contamination which minimizes the dilution of the internal standard cell solution. The result is lower maintenance needs and a longer time period between calibrations.

Built-in Preamp or Two-Wire Transmitter

The built-in preamp produces a strong signal, enabling you to locate the analyzer up to 3000 ft. (914 m) from the sensor. An optional built-in two-wire transmitter is available for applications requiring a 4-20 mA sensor signal. This option requires that the indicating instrument of the measuring system be capable of providing 24 VDC to power the sensor, and have adjustment means to calibrate for zero offset and span.

Versatile Mounting Styles

1.5 inch NPT threads are provided on both ends of the convertible mounting style sensor for either mounting into a pipe tee or attaching to the end of a pipe for immersion. The convertible style enables you to consolidate inventory, and thereby reduce associated costs. A union-mount style sensor and mounting tee are also available to conveniently install and remove the sensor for in-line service.

1 year warranty and 30 month pro-rated replacement

Specifications

Body material:	LCP
Cable Length:	90'
Electrode Material:	Glass
Mounting:	Convertible

What's in the box?

Includes: sensor with 90 ft cable and manual

Required Accessories

- sc200 Universal Controller: 100-240 V AC with one analog pH/ORP/DO sensor input and two 4-20 mA outputs (Item LXV404.99.00102)
- sc200 Universal Controller: 100-240 V AC (North America power cord) with two analog pH/ORP/DO sensor inputs, Modbus RS232/RS485 and two 4-20 mA outputs (Item LXV404.99.51112)